



# 4 IN 1 STYLUS PEN

The Belkin 4-in-1 STYLUS PEN adds versatility to your PDA. It includes a touch screen-sensitive stylus for navigation of your PDA, red and black ball-point pens, and a mechanical pen with eraser.

## How to use your 4-in-1 PDA Stylus Pen

1. The 4-in-1 Stylus Pen contains black and red ink ballpoint pens, a 0.5 mm mechanical pencil, and a PDA stylus.
2. To use the instrument you want, depress the top button. Under the button cover is an eraser. Simply pull the cap off to use.
3. To retract a pen, press the release button.
4. Located on the barrel of the pen are markings identifying the pens and pencil inside. BLACK - Black ink ballpoint pen, RED - Red ink ballpoint pen, 0.5 - 0.5 mm mechanical pencil, STYLUS - PDA stylus.



F8E708

## How to Select and Use the Pens/Pencil

1. Locate the instrument you want using the markings on the barrel of the pen.
2. Hold the desired marking so that it is facing up.
3. Depress the top button to engage the selected instrument.

## Replacing the Ballpoint Pens

1. Unscrew and remove the tip from the base of the pen.
2. With the pens/pencil exposed, locate the pen to replace; remove it by pulling it out of its barrel.
3. Insert the refill pen firmly into the open barrel; replace the pen tip.

## Feeding the Pencil Lead

1. Select the mechanical pencil instrument.
2. Hold the pen tip down.
3. Depress and release the top button in a pumping motion until the lead is the desired length.

## Refilling the Mechanical Pencil

1. Unscrew and remove the tip from the base of the pen.
2. With the pens/pencil exposed, locate the pencil; remove it by pulling it out of its barrel.
3. Add 0.5mm pencil leads to the open barrel; put the pencil tube back into place.
4. Replace the pen tip; follow steps on "Feeding Pencil Lead".

**Belkin Corporation**  
+1 310 898 1100  
Compton • CA • 90220 •  
USA

**Belkin Components, Ltd.**  
+44 (0) 1933 35 2000  
Shipton Way • Rushden • NN10 6GL •  
United Kingdom

© 2003 Belkin Corporation. All Rights Reserved.  
All trade names are registered trademarks of respective manufacturers listed.

P74270uk